

BELLA+CANVAS®


MEASUREMENT SPECIFICATION REPORT

Style No	FT044 (S/L): 3-Ply Barrier Mask
Fabrication	52% Airlume combed and ring-spun cotton, 48% Polyester, 32 Single, 4.2 oz. (2-Ply 8.4 oz.). Hydrophobic filter media.
Color	Charcoal, Deep Heather
Size	S/M, M/L

Wash/care instructions: Machine wash separately on hot. Only non-chlorine bleach. Machine dry medium heat separately. Medium iron. Do not dry clean. *Once this mask has been washed the hydrophobic filter membrane will no longer act as a liquid barrier.

IMPORTANT

The mask meets the surgical mask requirements only prior to washing. After the mask is washed, it should not be used (1) in any surgical setting or where significant exposure to liquid, bodily or other hazardous fluids may be expected; (2) in a clinical setting where the infection risk level through inhalation exposure is high; (3) for particulate filtration; or (4) in the presence of a high intensity heat source or flammable gas. Bella+Canvas, LLC makes no warranties, either express or implied, that the mask prevents infection or the transmission of viruses or diseases. As a face mask, the product has been authorized by FDA under an EUA for use as source control by the general public as well as by HCP in healthcare settings as to help prevent the spread of infection or illness during the COVID-19 pandemic. The product has not been FDA cleared or approved. This product is authorized only for the duration of the declaration that circumstances exist justifying the authorization of the emergency use of medical devices, including alternative products used as medical devices, during the COVID-19 outbreak, under section 564(b)(1) of the Act, 21 U.S.C. § 360bbb-3(b)(1) unless the authorization is terminated or revoked sooner.



	POM	Description	Placement	S/M	M/L
1	T43	CF Length - With Binding	On Fold - E to E - Along Curve	5 3/8	6 5/8
2	B68	Panel Width	Top - E to E - Along Curve	7 1/2	8 1/2
3	B68	Panel Width	Bottom - E to E - Along Curve	5 1/4	6 1/4
4	T194	Side Width	E to E - Inside Binding	2 1/8	2 5/8
5	T190B	Binding Length	Total	26 1/2	28 1/2
6	T190B	Binding Length	Ear Loop	6 7/8	6 7/8
7	T54	Binding Width		1/4	1/4